



33.311




Edge trim: Silicone black
Grip range: 1 - 2 mm
Hardness: SH 60
Insert: Wire 18 x 0,76 mm. Stainless can be done, min. 500 m
Heat resistant 200° C
Silicone is FDA conform

33.510




Edge trim: Silicone black
Grip range: 1 - 3 mm
Hardness: SH 60
Insert: Wire 26 x 0,76 mm. Stainless can be done, min. 500 m
Heat resistant 200° C
Silicone is FDA conform

33.312




Edge trim: Silicone black
Grip range: 2 - 4 mm
Hardness: SH 60
Insert: Wire. Stainless can be done, min. 500 m
Heat resistant 200° C
Silicone is FDA conform

33.429




Edge trim: Silicone black
Grip range: 3 - 6 mm (5 - 7 mm)
Hardness: SH 60
Insert: Wire 39 x 0,76 mm. Stainless can be done, min. 500 m
Heat resistant 200° C
Silicone is FDA conform

33.511




Edge trim: Silicone black
Grip range: 1,5 - 4 mm
Hardness: SH 50
Insert: Wire. Stainless can be done, min. 500 m
Heat resistant 200° C
Silicone is FDA conform

33.512




Edge trim: Silicone black
Grip range: 1 - 3,5 mm
Hardness: SH 50
Insert: Wire. Stainless can be done, min. 500 m
Heat resistant 200° C
Silicone is FDA conform

33.513




Edge trim: Silicone black
Grip range: 1,5 - 3,5 mm
Hardness: SH 50
Insert: Wire. Stainless can be done, min. 500 m
Heat resistant 200° C
Silicone is FDA conform

33.431A




Edge trim: Silicone light grey RAL 7035
Grip range: 2 - 4 mm
Hardness: SH 60/60 Solid balloon
Insert: Wire. Stainless can be done, min. 500 m
Heat resistant 200° C.
Silicone is FDA conform

33.514




Edge trim: Silicone
Grip range: 1,5 - 3 mm
Hardness: SH 75
Insert: Wire. Stainless can be done, min. 500 m
Heat resistant 200° C
Silicone is FDA conform

33.515




Edge trim: Silicone
Grip range: 1 - 2,5 mm
Hardness: SH 75
Insert: Wire. Stainless can be done, min. 500 m
Heat resistant 200° C
Silicone is FDA conform

33.516




Edge trim: Silicone
Grip range: 2 - 3 mm
Hardness: SH 75
Insert: Wire. Stainless can be done, min. 500 m
Heat resistant 200° C
Silicone is FDA conform

33.517




Edge trim: Silicone
Grip range: 2 - 3 mm
Hardness: SH 50
Insert: Wire. Stainless can be done, min. 500 m
Heat resistant 200° C
Silicone is FDA conform

33.518*




Edge trim: Silicone white
Grip range: 1,5 - 2,5 mm
Hardness: SH 60
Insert: Wire. Stainless can be done, min. 500 m
Heat resistant 200° C
Silicone is FDA conform
Min. order: 500 m

33.519




Edge trim: Silicone
Grip range: 1 - 2 mm
Hardness: SH 45
Insert: Wire. Stainless can be done, min. 500 m
Heat resistant 200° C
Silicone is FDA conform

33.520*



Edge trim: Silicone co-ex
Color: Black and redbrown
Grip range: 1,5 - 3 mm
Hardness: SH 60 / density 0,4
Insert: Wire. Stainless can be done, min. 500 m
Heat resistant 200° C
Min. order: 500 m

33.521




Edge trim: Silicone
Grip range: 1,5 - 4,5 mm
Hardness: SH 75
Insert: Wire. Stainless can be done, min. 500 m
Heat resistant 200° C
Silicone is FDA conform

* Skaffevare / Special order item


Kantenschutzprofile in Silikon

33.522 *




Edge trim: Silicone
 Grip range: 1 - 2,5 mm
 Insert: Wire. Stainless can be done, min. 500 m
 Heat resistant 200° C
 Silicone is FDA conform
 Min. order: 2.000 m

33.523 *




Edge trim: Silicone
 Grip range: 1,5 - 2,5 mm
 Hardness: SH 60
 Insert: Wire. Stainless can be done, min. 500 m
 Heat resistant 200° C
 Silicone is FDA conform
 Min. order: 500 m

33.524




Edge trim: Silicone
 Grip range: 2 - 4 mm
 Hardness: SH 50
 Insert: Wire. Stainless can be done, min. 500 m
 Heat resistant 200° C
 Silicone is FDA conform

33.525




Edge trim: Silicone
 Grip range: 3 - 6 mm
 Hardness: SH 50
 Insert: Wire. Stainless can be done, min. 500 m
 Heat resistant 200° C
 Silicone is FDA conform

33.526 *




Edge trim: Silicone
 Grip range: 1 - 2,5 mm
 Hardness: SH 65
 Insert: Wire. Stainless can be done, min. 500m
 Heat resistant 200° C
 Silicone is FDA conform

33.527




Edge trim: Silicone
 Grip range: 1 - 2,5 mm
 Hardness: SH 65
 Insert: Wire. Stainless can be done, min. 500m
 Heat resistant 200° C
 Silicone is FDA conform

33.528




Edge trim: Silicone
 Grip range: 1 - 3 mm
 Hardness: SH 60
 Insert: Wire. Stainless can be done, min. 500m
 Heat resistant 200° C
 Silicone is FDA conform

33.529 *




Edge trim: Silicone
 Grip range: 1 - 1,5 mm
 Hardness: SH 80
 Insert: Wire. Stainless can be done, min. 500 m
 Heat resistant 200° C
 Silicone is FDA conform
 Min. order: 500 m

33.530




Edge trim: Silicone
 Grip range: 3,5 - 5 mm
 Hardness: SH 70
 Insert: Wire. Stainless can be done, min. 500 m
 Heat resistant 200° C
 Silicone is FDA conform

33.531 *



Edge trim: Silicone
 Grip range: 2,5 - 5,5 mm
 Hardness: SH 70
 Insert: Wire. Stainless can be done, min. 500 m
 Heat resistant 200° C
 Silicone is FDA conform
 Min. order: 500 m

33.532







Edge trim: Silicone
 Grip range: 5,5 - 6,5 mm
 Hardness: SH 65
 Insert: Wire. Stainless can be done, min. 500 m
 Heat resistant 200° C
 Silicone is FDA conform

Silikonprofile

Hent kataloget med silikoneskæffeprofiler på vores hjemmeside. bibus.de

Download the catalog with silicone order profiles on our homepage. bibus.de

Group 0010 	Group 0021 	Group 0023 	Group 0107 	Group 0030 
Group 0011 	Group 0175 	Group 0201 	Group 0106 	Group 0120 
Group 0012 	Group 0022 	Group 0024 	Group 0209 	Group 0124 
Group 0020 	Group 0101 	Group 0025 	Group 0111 	Group 0126 
Group 0121 	Group 0100 	Group 0109 	Group 0110 	Group 0125 
Group 0139 	Group 0108 	Group 0153 	Group 0112 	Group 0160 
Group 0150 	Group 0186 	Group 0169 	Group 0192 	Group 0159 
Group 0178 	Group 0113 	Group 0208 	Group 0214 	Group 0119 

Silikonprofile

Group 0102 	Group 0104 	Group 0129 	Group 0127 	Group 0171
Group 0517 	Group 0145 	Group 0130 	Group 0191 	Group 0516
Group 0102A 	Group 0179 	Group 0131 	Group 0206 	Group 0144
Group 0103 	Group 0105 	Group 0132 	Group 0134 	Group 0194
Group 0103A 	Group 0172 	Group 0133 	Group 0211 	Group 0147
Group 0146 	Group 0188 	Group 0181 	Group 0167 	Group 0128
Group 0199 	Group 0158 	Group 0170 	Group 0140 	Group 0137
Group 0155 	Group 0141 	Group 0207 	Group 0508 	Group 0148

Silikonprofile

Group 0122 	Group 0176 	Group 0177 	Group 0143 	Group 0164
Group 0123 	Group 0197 	Group 0165 	Group 0117 	Group 0166
Group 0157 	Group 0173 	Group 0182 	Group 0187 	Group 0138
Group 0151 	Group 0189 	Group 0190 	Group 0115 	Group 0196
Group 0200 	Group 0152 	Group 0215 	Group 0210 	Group 0205
Group 0180 	Group 0168 	Group 0198 	Group 0213 	Group 0163
Group 0156 			Group 0142 	Group 0154
				Group 0512

Silikonprofile

Group 0193 	Group 0183 	Group 0202 	Group 0116 	Group 0510
Group 0193 	Group 0514 	Group 0195 	Group 0501 	
Group 0174 	Group 0507 	Group 0203 	Group 0502 	
Group 0184 		Group 0212 	Group 0503 	
Group 0184 	Group 0118 	Group 0185 	Group 0504 	
Group 0513 	Group 0161 	Group 0204 	Group 0505 	
Group 0136 	Group 0515 	Group 0511 	Group 0506 	
Group 0135 			Group 0509 	